# **TECHNICAL DATA SHEET**

## MelOx-NGen




### **DESCRIPTION**

MelOx-NGen provides high oxygen barrier performance to eco-friendly packaging products based on paper, paperboard, plastics, or biopolymers. This product offers excellent oxygen and oil & grease barrier performance in both typical and tropical conditions.

PROPERTIES	VALUE
Product form	Water suspension
Solid content (wt%)	20 ± 2
Preservative	Included
Antifoam agent	Included
рН	5-8
Viscosity (cP, Brookfield, S63, 100 rpm, RT)	400 ± 200

### **BARRIER PROPERTIES FOR COATED SUBSTRATE**

Conditions/Coated substrate	Paper	BOPP	PE	PET	Test method
OTR @ 23 °C, 0% RH (cc/m²-day-atm)	< 0.5	< 1	< 1	< 0.5	ASTM D3985 and F1927-50
OTR @ 23 °C, 50% RH (cc/m²·day·atm)	< 0.5	< 1	< 1	< 0.5	ASTM D3985 and F1927-50
OTR @ 23 °C, 70% RH (cc/m²·day·atm)	< 5				ASTM D3985 and F1927-50
Oil & grease barrier (KIT rating)	12				TAPPI T 559 pm-96
	<b>✓</b>				PTS-RH 021:2012
Recyclability on paper	<b>~</b>				CEPI recyclability laboratory test method Version 2



Melodea Ltd. All Rights Reserved© Proprietary Information

## **TECHNICAL DATA SHEET**

### MelOx-NGen



### **HOW TO USE**

- Ready for use as is. It is highly recommended that the suspension not be modified.
- Do not heat the suspension to above 40 °C. When drying, follow the recommended drying temperature (see User Guide).
- Mix the suspension well before applying, to assure homogeneity and fluidity. An IBC mixer is recommended for IBCs.
- MelOx-NGen should be applied on the substrate, and a top layer should be applied on top of it, as illustrated in the figure above. For paper, use VBseal, and for plastic, lamination or metallization.
- When applying on paper, it is recommended to apply a total dry coating weight of  $\sim$ 5 g/m<sup>2</sup>. On plastic substrates, one thin layer (< 2  $\mu$ m) will suffice (see User Guide for detailed utilization instructions).
- The most suitable coating technologies are rod-coater, gravure, slot-die, flexo, and curtain coating.
- Reusing or storing the used material from the machine is not recommended.

#### STORAGE & SHELF LIFE

- Exhibits good shelf-life stability of at least 9 months in suspension form (in an unopened container, when stored correctly), and at least 1 year as a dry coated layer.
- Delivered in drums or IBC's.
- The product should be stored under cool but frost-free conditions (between 5  $^{\circ}$ C and 25  $^{\circ}$ C), away from direct sunlight.
- Storage at low temperature may increase the product's viscosity and cause reversible gelation. Acclimatization for 1-2 days at 20-25 °C will decrease the viscosity to its original state.